


Structure and Ordering Information



Product	Outer Diameter	Catalog No.	Usable Length	Tip Shape
ASAHI Silverway	0.89mm (0.035 inch)	SA0035N15S	150cm	Angled
		SA0035N18S	180cm	Angled
		SA0035N20S	200cm	Angled
		SA0035N22S	220cm	Angled
		SA0035N26S	260cm	Angled
		SA0035N30S	300cm	Angled
		SJ1535N15S	150cm	J-shape1.5mm
		SJ1535N18S	180cm	J-shape1.5mm
		SJ1535N20S	200cm	J-shape1.5mm
		SJ1535N22S	220cm	J-shape1.5mm
		SJ1535N26S	260cm	J-shape1.5mm
		SJ1535N30S	300cm	J-shape1.5mm
		SJ3035N15S	150cm	J-shape3.0mm
		SJ3035N18S	180cm	J-shape3.0mm
		SJ3035N20S	200cm	J-shape3.0mm
		SJ3035N22S	220cm	J-shape3.0mm
		SJ3035N26S	260cm	J-shape3.0mm
		SJ3035N30S	300cm	J-shape3.0mm



© 2019 ASAHI INTECC CO., LTD.
"ASAHI", "ACT ONE" and "Silverway" are trademarks or registered trademarks of ASAHI INTECC CO., LTD. in Japan and other countries.
Coated with SLIP-COAT® coating.

Manufactured by:



ASAHI INTECC CO.,LTD.

3-100 Akatsuki-cho, Seto, Aichi 489-0071 Japan

Contact phone number: +81-561-86-9101

www.asahi-intecc.com

Distributed by:

ASAHI Silverway

Hydrophilic Coated Spring Coil Guide Wire

with **ACT ONE**



ASAHI Silverway


Hydrophilic Coated Spring Coil Guide Wire

with **ACT ONE**

ASAHI's newly developed 0.89mm (0.035") spring coil guide wire with ACT ONE technology.

Double Coil Structure



Double coil structure improves durability and maneuverability



Hybrid Shaft Design

ACT ONE on proximal shaft

ASAHI's technologies are incorporated in the proximal shaft enabling Silverway to achieve outstanding torque performance.



Testing method

The input and output angle of the GW rotation when it is inserted into a looped catheter and the proximal shaft is rotated. The length from the tip to the machine is kept equal.

Hybrid coating design

Safety

Distal shaft : Silicone - tactile feedback

Distal 15cm is coated with silicone material for better safety.

Maneuverability

Mid shaft : Hydrophilic - smooth delivery

Hydrophilic coated mid shaft provides superior lubricity to facilitate smooth delivery.

Controlability

Proximal shaft : Silicone - wire handling

Silicone coated proximal shaft for adequate lubricity and better guide wire handling.

Silicone coating



ACT ONE


ASAHI brand multi wire coil provides torque force, torque response, durability and flexibility.

Safety

Soft & Radiopaque tip

Silverway's highly flexible and radiopaque tip is designed to be less traumatic and easier to visualize.

Tip Flexibility



Testing method

The maximum force needed to bend the GW at 3 points 10mm from the tip when pushed.

Maneuverability

Tip shape

The tip shape of both J-shape and Angled can be stretched easily by hand. It can be inserted into the Y-connector without the use of an inserter.

