


## Structure and Ordering Information



# ASAHI Silverway

Hydrophilic Coated Spring Coil Guide Wire

with **ACT ONE**

<b>ASAHI Silverway</b>	0.89mm (0.035 inch)	SA0035N15S	150 <sub>cm</sub>	Angled
		SA0035N18S	180 <sub>cm</sub>	Angled
		SA0035N20S	200 <sub>cm</sub>	Angled
		SA0035N22S	220 <sub>cm</sub>	Angled
		SA0035N26S	260 <sub>cm</sub>	Angled
		SA0035N30S	300 <sub>cm</sub>	Angled
		SJ1535N15S	150 <sub>cm</sub>	J-shape1.5mm
		SJ1535N18S	180 <sub>cm</sub>	J-shape1.5mm
		SJ1535N20S	200 <sub>cm</sub>	J-shape1.5mm
		SJ1535N22S	220 <sub>cm</sub>	J-shape1.5mm
		SJ1535N26S	260 <sub>cm</sub>	J-shape1.5mm
		SJ1535N30S	300 <sub>cm</sub>	J-shape1.5mm
		SJ3035N15S	150 <sub>cm</sub>	J-shape3.0mm
		SJ3035N18S	180 <sub>cm</sub>	J-shape3.0mm
		SJ3035N20S	200 <sub>cm</sub>	J-shape3.0mm
		SJ3035N22S	220 <sub>cm</sub>	J-shape3.0mm
		SJ3035N26S	260 <sub>cm</sub>	J-shape3.0mm
		SJ3035N30S	300 <sub>cm</sub>	J-shape3.0mm



© 2019 ASAHI INTECC CO., LTD.  
"ASAHI", "ACT ONE" and "Silverway" are trademarks or registered trademarks of ASAHI INTECC CO., LTD. in Japan and other countries.  
Coated with SLIP-COAT® coating.

Manufactured by:



**ASAHI INTECC CO.,LTD.**

3-100 Akatsuki-cho, Seto, Aichi 489-0071 Japan

Contact phone number: +81-561-86-9101

www.asahi-intecc.com

Distributed by:



K19248\_B\_CE\_1.0



# ASAHI Silverway


Hydrophilic Coated Spring Coil Guide Wire

with **ACT ONE**

ASAHI's newly developed 0.89mm (0.035") spring coil guide wire with ACT ONE technology.

## Double Coil Structure



Double coil structure improves durability and maneuverability



## Hybrid Shaft Design

### ACT ONE on proximal shaft

ASAHI's technologies are incorporated in the proximal shaft enabling Silverway to achieve outstanding torque performance.



**Testing method**  
The input and output angle of the GW rotation when it is inserted into a looped catheter and the proximal shaft is rotated. The length from the tip to the machine is kept equal.

## Hybrid coating design

### Safety

**Distal shaft : Silicone - tactile feedback**  
Distal 15cm is coated with silicone material for better safety.

### Maneuverability

**Mid shaft : Hydrophilic - smooth delivery**  
Hydrophilic coated mid shaft provides superior lubricity to facilitate smooth delivery.

### Controlability


**Proximal shaft : Silicone - wire handling**  
Silicone coated proximal shaft for adequate lubricity and better guide wire handling.



**ACT ONE**  
ASAHI brand multi wire coil provides torque force, torque response, durability and flexibility.

## Safety


**Soft & Radiopaque tip**  
Silverway's highly flexible and radiopaque tip is designed to be less traumatic and easier to visualize.



**Testing method**  
The maximum force needed to bend the GW at 3 points 10mm from the tip when pushed.

## Maneuverability

**Tip shape**  
The tip shape of both J-shape and Angled can be stretched easily by hand. It can be inserted into the Y-connector without the use of an inserter.



Silicone coating

Hydrophilic coating  
SLIP-COAT®